



Product Service

# CERTIFICATE

No. Z1A 16 07 79614 015

**Holder of Certificate: GARANT Productions GmbH**Otto-Knecht-Str. 3  
72766 Reutlingen  
GERMANY**Certification Mark:****Product: Workshop furniture****Tested according to:** PPP 51021B:2015  
AfPS GS 2014:01 PAK

The product meets the safety and health requirements of the German Product Safety Act section 20 to 22 ProdSG. The certification marks shown above can be affixed on the product. It is not permitted to alter the certification marks in any way. In addition the certificate holder must not transfer the certificate to third parties. This certificate is valid until the listed date, unless it is cancelled earlier. See also notes overleaf.

**Test report no.:** 713084004-2**Valid until:** 2021-07-14**Date,** 2016-07-26  
( Harald Bardowicks )

Page 1 of 2

**CERTIFICATE**

No. Z1A 16 07 79614 015

**Model(s):****Computer workstations****Art.-no. 951010, 951470, 951502, 951503****Parameters:**

Computer workstation mobile

Art.-no. 95 1010:

Max. permissible load lower shelf:	12 kg (distributed load)
Height:	1400 mm
Width:	750 mm
Depth:	550 mm
Sheet thickness:	0.9 mm
With Wheels (4 fixed casters, two steered and braked)	

Computer Workstation in several national versions

Art.-no. 95 1470:

Max. permissible load:	300 kg
Rated voltage socket outlet:	250 V AC
Rated current socket outlet:	16 A
Rated voltage ventilator:	230 V; 50 Hz
Rated current ventilator:	70 mA
Rated power ventilator:	12 W
Height:	1620 mm
Width:	750 mm
Depth:	550 mm
Clear height of the monitor housing:	460 mm
Clear width of the monitor housing:	690 mm
Usable depth of the monitor housing:	230 mm
Clear height of the base cabinet:	840 mm
Clear width of the base cabinet:	690 mm
Weight:	73 kg
Sheet thickness:	0.9 mm

Computer workstation and  
Computer workstation with printer flap  
in several national versions

Art.-no. 951502 und 951503

Max. permissible load:	300 kg
Rated voltage socket outlet:	250 V AC
Rated current socket outlet:	16 A
Rated voltage ventilator:	230 V; 50 Hz
Rated current ventilator:	70 mA
Rated power ventilator:	12 W
Height:	1740 mm
Width:	750 mm
Depth:	550 mm
Clear height of the monitor housing:	460 mm
Clear width of the monitor housing:	690 mm
Usable depth of the monitor housing:	230 mm
Clear height of the base cabinet:	640 mm
Clear width of the base cabinet:	690 mm
Dimension printer flap:	236 x 290 mm (art.-no. 95 1503)
Weight:	73 kg
Sheet thickness:	0.9 mm

**Factory(ies):**

79614

Page 2 of 2