



asecos® Containment trays – plastic for 1000 litre IBC

Of polyethylene (PE) – light, weatherproof, robust.

Standard: Approved by the DIBt, Berlin, according to the General Building Regulations and declaration of conformity (ÜHP).

Application: For secure storage of containers **IBC** (Intermediate Bulk Containers) and **CTC** (Cubic Tank Containers). **For storage of water-polluting liquids of GHS categories 1 – 4.** Especially **resistant to acids, alkalis** and oils. Depending on the tare weight of the IBC/CTC, suitable for liquids with a maximum specific weight of 1800 kg/m³.

Storage of flammable media is not permitted (applies to Germany).



Containment trays for 1000 litre IBC

Number of IBC×IBC Contents (l)		1×1000	2×1000
96l	98 1440 Containment tray for 1000 litre IBC without platform	–	XXX
96l	98 1445 Containment tray for 1000 litre IBC with PE platform	XXX	XXX
Drip catch volume	l	1100	
Height	mm	970	720
Width	mm	1430	2280
Depth	mm	1430	
Load capacity per storage position	kg	2000	
Weight	kg	105	180



Number of IBC×IBC Contents (l)		2×1000
96l	98 1460 Containment tray for 1000 litre IBC with galvanised grid	XXX
96l	98 1465 Containment tray for 1000 litre IBC with PE grid	XXX
Drip catch volume	l	1000
Height	mm	490
Width	mm	2480
Depth	mm	1410
Load capacity per storage position	kg	2000

