



Pneumatic scriber DynaPen®, Manufacturer's designation: 10850



Order data

| | |
|--------------|--------------|
| Order number | 079708 10850 |
| GTIN | 616026108509 |
| Item class | 03R |

Description

Version:

DynaPen pencil-sized pneumatic pen with a **comprehensive accessories set (1/8 inch)**. The pulsating drive movement (amplitude 0.018 mm) permits **many applications** such as engraving, lettering, light cleaning, and filing work, as well as deburring etc.

Supplied with:

1.4 m connection hose, 3 files, engraving tip, and a hexagon key.

Note:

See No. 529420 for suitable diamond mini-files.

maximum air consumption: 28.2 l/min

Impact frequency: 233 Hz

Thread of the compressed air connection port: 1/4 inch NPT inch

Weight: 0.26 kg

Operating noise: 79 dB(A)

maximum vibration to EN: 8 m/s²

Technical description

| | |
|--|-------------------|
| Weight | 0.26 kg |
| Ø | 23 mm |
| Manufacturer's designation | 10850 |
| Thread of the compressed air connection port | 1/4 inch NPT inch |
| Impact frequency | 233 Hz |

| | |
|-------------------------|--------------------|
| maximum air consumption | 28.2 l/min |
| maximum vibration to EN | 8 m/s ² |
| Operating noise | 79 dB(A) |
| Length | 108 mm |