

LESSMANN®
THE GERMAN BRUSH COMPANY**End brush pointed, steel wire 0.30 mm, Brush Ø: 12 mm****Order data**

Order number	574790 12
GTIN	4017359068564
Item class	57L

Description**Version:**

Brush head of waved wire, pointed at a **25° angle**. **Shank Ø 6 mm**.

Application:

In straight die grinders or flexible shafts. **For working in corners and recesses.**

Bristle height: 20 mm

maximum speed: 20000 rpm

Technical description

maximum speed	20000 rpm
Bristle height	20 mm
Bristle thickness	0.3 mm
Shank Ø	6 mm
Brush material	Steel wire