



## Electronics side cutter, mirror-polished, round head, FW, overall length: 115 mm



### Order data

|              |               |
|--------------|---------------|
| Order number | 726435 115    |
| GTIN         | 4003773025092 |
| Item class   | 73F           |

### Description

#### Version:

Mirror polished, therefore no faults in the circuit due to peeling chrome plate. Sturdy box joint with zero play. Low-friction double spring for smooth and gentle opening. Multi-component grips, black/grey, electrically conductive. **Suitable for ESDs.**

#### Application:

For making precision cuts, e.g. in electronics and precision mechanisms.

#### Standard:

DIN ISO 9654

#### Material:

Ball-bearing steel, cutting edges induction hardened.

electrical insulation: EGB/ESD

Cutting chamfer: fine bevel

Material: Ball bearing steel

Head width: 11 mm

Cutter length: 14 mm

Cutting capacity hard wire up to  $\varnothing$ : 0.3 - 0.6 mm

Cutting capacity copper wire up to  $\varnothing$ : 0.3 - 1.6 mm

Cutting capacity medium hard wire up to  $\varnothing$ : 0.3 - 1.2 mm

### Technical description

|                |        |
|----------------|--------|
| Head width     | 11 mm  |
| overall length | 115 mm |

|   |   |
|---|---|
| Cutting capacity copper wire up to Ø      | 0.3 - 1.6 mm                                      |
| Cutter length                             | 14 mm   |
| Cutting capacity hard wire up to Ø        | 0.3 - 0.6 mm                                      |
| Cutting capacity medium hard wire up to Ø | 0.3 - 1.2 mm                                      |
| electrical insulation                     | EGB/ESD   |
| Cutting chamfer                           | fine bevel  |
| Material                                  | Ball bearing steel                                |
| Head shape                                | round   |
| Norm                                      | DIN ISO 9654                                      |
| Handle                                    | Multi-component grips                             |
| Manufacturing process                     | Cutting edges induction hardened (approx. 62 HRC) |
| Surface                                   | mirror polished                                   |
| Product name attribute                    | FW  |
| with return spring                        | yes   |