



Carrier jaw fixed, for type: 160



Order data

Order number	361332 160
GTIN	4250364402965
Item class	34A

Description

Application:

The carrier jaw allows mounting of wedges and various different gripp inserts. Wedges, gripp inserts and gripp sets can be screwed into a variety of hole patterns for secure clamping of various workpiece geometries.

Suitable for :

NC high pressure vice No. 361302 / 1304.

Note:

Wedge mountings + accessories No. 361341 – 361352, gripp inserts No. 361238 – 361250.

Jaw width b: 122.5 mm

c: 30 mm

Jaw height h: 25 mm

Jaw length l: 250 mm

suitable for colour code: Titan 2

suitable for colour code: LCV125G

Technical description

for type	160
Jaw width b	122.5 mm
c	30 mm
Jaw height h	25 mm

Jaw length l	250 mm
suitable for colour code	Titan 2
suitable for colour code	LCV125G