



## Precision cylinder lock with lock barrel, shared key, Body Ø: 45 mm



### Order data

Order number	085812 45
GTIN	2050000971945
Item class	08P

### Description

#### Version:

Precision padlock, brass body nickel-plated, shackle made of hardened steel, chrome-plated, and double locked. With integrated lock barrel No. 950050 (not for No. 085816) for individual configuration / integration into your existing DOM locking system. Can be individually fitted using lock barrel No. 950050 to suit your requirements.

#### Note:

For individually configurable lock barrels see No. 950050 / 950072, **group 95 in the Workstations and Storage catalogue volume 3.**

Hoop Ø: 6 mm

### Technical description

Shackle, double lever mechanism	yes
Material of the band	Steel
Material of the housing	Nickel-plated brass
Security logic	shared keys
Number of keys	2
Supplied without lock barrel	no

Number combinations can be selected individually.	no
Body Ø	45 mm
Lock number range	HO 001 - 200
suitable for lock barrels	Yes
Lock numbers individually interchangeable	yes
Type of locking	Cylinder lock
Hoop hardened	yes
compatible with integrated locking systems	yes
Hoop Ø	6 mm