



## Compressed air and liquid blow gun, adjustable Air connection



### Order data

Order number	080252
GTIN	7391390264053
Item class	08A

### Description

#### Version:

Compressed air guns with steplessly adjustable air flow, low weight, flexible suspension options, and easy handling.

**Compressed air and liquid blow gun** with jet nozzle, **adjustable jet** (point to flat) **controllable flow** (air: 200 -1200 ltr/min, liquid: 7– 46 ltr/min).

Supplied with steel coupling adapter 1/4 inch.

#### Note:

**The CEJN series 320 satisfies Euro standard 7.6 (nominal Ø 7.6 mm, Euro profile) and is compatible with all popular systems.**

Flow rate: 200 - 1200 l/min

### Technical description

Flow rate	200 - 1200 l/min
Liquid flow rate	7 - 46 l/min
Air flow rate	200 - 1200 l/min

