



XDLT 120408 ER, HB7635, Type: INOX



Order data

Order number	212979 INOX
GTIN	4045197581822
Item class	21A

Description

Note:

Standard application values for $a_e = 0.5 \dots 1 \times D / a_{p \max}$
 maximum cutting depth $a_{p \max}$: 1.8 mm
 Feed f_z per tooth: 1.07 mm
 ISO code indexable insert: XDLT 120408 ER
 Type: INOX
 Programming radius at $a_{p \max}$: 2.6 mm

Technical description

Type	INOX
ISO code indexable insert	XDLT 120408 ER
Programming radius at $a_{p \max}$	2.6 mm
maximum cutting depth $a_{p \max}$ when slot milling from solid	1.8 mm
maximum cutting depth $a_{p \max}$ when side milling	1.8 mm
Series	FeedKing

Grade	HB7635
Tool material	Carbide
maximum cutting depth $a_{p\max}$	1.8 mm
Feed f_z per tooth	1.07 mm