


BDMT 070308 ER-JT, PR1210, Type: GG

Order data

Order number	227157 GG
GTIN	4960664622597
Item class	25A

Description
Note:

Standard application values for $a_e = 0.3 \times D$. Exactly 90° up to $a_p = 4$ mm.

Feed f_z per tooth: 0.09 – 0.16 mm

maximum cutting depth $a_{p,max}$ when slot milling from solid: 4 mm

Technical description

Feed f_z per tooth	0.09 – 0.16 mm
Type	GG
maximum cutting depth $a_{p,max}$ when side milling	4 mm
maximum cutting depth $a_{p,max}$ when slot milling from solid	4 mm
Series	End / face mill
ISO code indexable insert	BDMT 070308 ER-JT
Grade	PR1210
Tool material	Carbide

