


**BDMT 11T308 ER-N2, PR1210, Type: GG**

**Order data**

Order number	227480 GG
GTIN	4960664622603
Item class	25A

**Description**
**Note:**

The milling cutters are alternately equipped with equal numbers of indexable inserts shape N2 and N3. Please fit the inserts as marked on the body.

Standard application values for  $a_e = 0.3 \times D$ .

Feed  $f_z$  per tooth: 0.09 – 0.2 mm

maximum cutting depth  $a_{p\max}$  when slot milling from solid: 8 mm

**Technical description**

Type	GG
Feed $f_z$ per tooth	0.09 – 0.2 mm
maximum cutting depth $a_{p\max}$ when side milling	8 mm
maximum cutting depth $a_{p\max}$ when slot milling from solid	8 mm
Series	End / face mill
ISO code indexable insert	BDMT 11T308 ER-N2
Grade	PR1210

Tool material

Carbide