


APMT 133508 TR, HB7520, Type: UNI

Order data

Order number	215381 UNI
GTIN	4045197601377
Item class	21A

Description
Note:

Standard application values for $a_e = 0.25 \times D$ / $a_p = 4$ mm, $a_{p,max} = 6$ mm.
 maximum cutting depth $a_{p,max}$ when slot milling from solid: 6 mm

Technical description

Type	UNI
maximum cutting depth $a_{p,max}$ when side milling	13 mm
maximum cutting depth $a_{p,max}$ when slot milling from solid	6 mm
Series	Softcut®
ISO code indexable insert	APMT 133508 TR
Grade	HB7520
Tool material	Carbide

