


APMT 133524 SR, HB7510, Type: ST1400

Order data

Order number	215329 ST1400
GTIN	4045197673596
Item class	21A

Description
Note:

Standard application values for $a_e = 0.25 \times D$ / $a_p = 4$ mm, $a_{p,max} = 6$ mm.

Feed f_z per tooth: 0.15 mm

maximum cutting depth $a_{p,max}$ when slot milling from solid: 6 mm

Technical description

Feed f_z per tooth	0.15 mm
Type	ST1400
maximum cutting depth $a_{p,max}$ when side milling	13 mm
maximum cutting depth $a_{p,max}$ when slot milling from solid	6 mm
Series	Softcut®
ISO code indexable insert	APMT 133524 SR
Grade	HB7510
Tool material	Carbide

