


**APMT 060204 FR, HU7810, Type: ALU**

**Order data**

Order number	215623 ALU
GTIN	4045197601414
Item class	21A

**Description**
**Note:**

Standard application values for  $a_e = 0.25 \times D$ .  $a_p = 3$  mm,  $a_{p \max} = 4$  mm.

Feed  $f_z$  per tooth: 0.1 mm

maximum cutting depth  $a_{p \max}$  when slot milling from solid: 4 mm

**Technical description**

Type	ALU
Feed $f_z$ per tooth	0.1 mm
maximum cutting depth $a_{p \max}$ when side milling	6 mm
maximum cutting depth $a_{p \max}$ when slot milling from solid	4 mm
Series	Softcut®
ISO code indexable insert	APMT 060204 FR
Grade	HU7810
Tool material	Carbide

