


APKT 16..08 PDFR, HU7710, Type: ALU

Order data

Order number	215728 ALU
GTIN	4045197410948
Item class	21A

Description
Note:

Standard application values apply for milling cutters No. 215705 to 215715: $a_e = 0.3 \times D$ / $a_{p\max} = 7$ mm.

Worktop thickness: 5.05 mm

Feed f_z per tooth: 0.18 mm

maximum cutting depth $a_{p\max}$ when slot milling from solid: 7 mm

Technical description

suitable holder	AP..1604
Feed f_z per tooth	0.18 mm
Type	ALU
maximum cutting depth $a_{p\max}$ when side milling	7 mm
maximum cutting depth $a_{p\max}$ when slot milling from solid	7 mm
Series	Chamfer mill
Series	Indexable end mill

ISO code indexable insert	APKT 16..08 PDFR
Grade	HU7710
Tool material	Carbide
Worktop thickness	5.05 mm