



Boring bar set carbide, left-hand



Order data

Order number	260019
GTIN	4045197651945
Item class	29W

Description

Boring bar set carbide ISO code toolholder: E08K SCLCR/L06

ISO code toolholder: E10K SCLCR/L06

ISO code toolholder: E12M SCLCR/L06

suitable indexable insert: CC.. 0602..

Minimum pre-drill $\varnothing D_{\min}$: 12 mm

Minimum pre-drill $\varnothing D_{\min}$: 14 mm

Technical description

Minimum pre-drill $\varnothing D_{\min}$	12 mm
Minimum pre-drill $\varnothing D_{\min}$	14 mm
Minimum pre-drill $\varnothing D_{\min}$	10 mm
Centre-line offset	8 mm
Centre-line offset	5 mm
Centre-line offset	6 mm
Pack of insert screws	269413
suitable indexable insert	CC.. 0602..
ISO code toolholder	E08K SCLCR/L06

ISO code toolholder	E10K SCLCR/L06
ISO code toolholder	E12M SCLCR/L06
Overall length	150 mm
Overall length	125 mm
Overall length	125 mm
Clamping height H	11.5 mm
Clamping height H	7.6 mm
Clamping height H	9.6 mm
Application type	left-hand
Boring depth up to	8×D
Tool material	Carbide
Norm	DIN 8024
Through-coolant	true

Accessories

Set of insert screws 10 pieces	269413
--------------------------------	--------