



Copying insert, internal, left-hand, L1 = 30 mm, Ø Dmin: 6,2 mm



Order data

Order number	270298 6,2
GTIN	4045197466631
Item class	21I

Description

Copying insert, internal, left-hand 6,2 mm Shank Ø d: 6 mm
 Tip centre offset F: 2.95 mm
 maximum cutting depth t_{max} : 1.75 mm
 Radius R: 0.2 mm

Technical description

Shank Ø d	6 mm
Tip centre offset F	2.95 mm
maximum cutting depth t_{max}	1.75 mm
Minimum Ø D_{min}	6.2 mm
Radius R	0.2 mm
Overhang L_1	30 mm
Product name attribute	$L_1 = 30$ mm