

SWISS TOOLS

Toolholder axial, single, right-hand, HSK-T 40, for toolholder square: 20 mm



Order data

Order number	318602 20
GTIN	2050001714237
Item class	36D

Description

Version:

With adjustable cooling nozzle with internal thread.

Application:

For use on lathes and milling centres.

For mounting ISO toolholders with square shanks.

Arbor standard: ISO 12164-3

Through-coolant: true

Overhang dimension A: 80 mm

Clamping length L_1 : 45 mm

B: 30 mm

External \varnothing D: 80 mm

Technical description

B	30 mm
for toolholder square	20 mm
Clamping length L_1	45 mm
Overhang dimension A	80 mm
External \varnothing D	80 mm
Capacity	HSK-T 40
Arbor standard	ISO 12164-3

Through-coolant

true