

BMI®
Laser spirit level, Length: 240 mm

Order data

Order number	468460 240
GTIN	4007368096207
Item class	460

Description
Version:

Robust, easy to use aluminium housing with 3 point lasers at angles of 90° to each other. The accuracy of the vials and laser in relation to the measuring face is 0.2 mm / m. Four powerful magnets are inset in the base. Contact surface with laser reference edge (edge = centre of laser).

Application:

For quick alignment, marking, and levelling.

Supplied with:

Alignment plate for uneven ground. 3 batteries No. 081556 size LR3.

Error limit: 0.2 mm/m

Laser class: 2

Range: 30 m

Threaded socket for stand: 1/4 inch

Width: 25 mm

Height: 44 mm

Technical description

Width	25 mm
Length	240 mm
Laser class	2
Threaded socket for stand	1/4 inch

Range	30 m
Height	44 mm
Batteries / rechargeable batteries included	081556 LR3
Number of batteries contained	3
Error limit	0.2 mm/m
Measurement technology	analogue

Services

Labelling laser-etched	018940
------------------------	--------

Accessories

Alkaline-manganese batteries International size LR3	081556 LR3
-----------------------------------------------------	------------