

BMI®**Pocket spirit level PICO, Length of steel tape measure: 1 m****Order data**

Order number	467476 1
GTIN	4007368110569
Item class	46M

Description**Version:**

Ideal for precise marking out in the horizontal plane. The steel tape measure can be stopped at any point appropriate to the measurement application. With magnet on the base and side face.

Supplied with:

Pocket spirit level including steel tape measure No. 461830 size 1000.

Error limit in normal position: 1 mm/m

Length: 62 mm

Width: 25 mm

Height: 66 mm

Technical description

Width	25 mm
Length of steel tape measure	1 m
Length	62 mm
Error limit in normal position	1 mm/m
Height	66 mm

Accessories

Roll-up steel tape measure Band length 1000 mm

461830 1000