


LOEU 130708 TR-H, HB7710, Type: GG

Order data

| | |
|--------------|---------------|
| Order number | 215147 GG |
| GTIN | 4045197866882 |
| Item class | 21A |

Description
Note:

Standard application values for $a_e = 0.3 \times D$ / $a_p = 10$ mm

ISO code indexable insert: LOEU 130708 TR-H

Feed f_z : 0.24 mm

Technical description

| | |
|--|--|
| Feed f_z | 0.24 mm |
| ISO code indexable insert | LOEU 130708 TR-H |
| maximum cutting depth $a_{p,max}$ when side milling | 10 mm |
| maximum cutting depth $a_{p,max}$ when slot milling from solid | 10 mm |
| Series | Tangential high-performance indexable end mill |
| Grade | HB7710 |
| Tool material | Carbide |

