



Short drill chuck, PSC 40, Clamping range: 0,3-10 mm



Order data

Order number	308587 0,3-10
GTIN	4045197868817
Item class	31B

Description

Version:

- **With Balluffchip bore.**
- **All shanks hard turned (for smooth running!).**
- **Mating faces of the PSC internal contour machined.**
- **For clockwise and anticlockwise rotation.**
- **Sand-blasted.**

Max. slim chucks for the most common \varnothing 0.3 – 10.2 mm.

Supplied with:

Clamping wrench.

Optional extras:

Coolant pipe and plug-in socket No. 309885 / 9893.

Arbor standard: ISO 26623-2

Through-coolant: Yes

Balance quality G at rotational speed: G 2.5 at 18,000 rpm

Concentricity: $\leq 3 \mu\text{m}$

maximum tightening torque $M_{d,max} \leq 14 \text{ N}\cdot\text{m}$

Overhang dimension A: 74 mm

External \varnothing D: 36 mm

Spare hexagon screwdriver 627425: 4 AF

Technical description

External \varnothing D	36 mm
Overhang dimension A	74 mm

Clamping range	0.3 - 10.2 mm
Spare hexagon screwdriver 627425	4 AF
Capacity	PSC 40
Arbor standard	ISO 26623-2
Through-coolant	Yes
Balance quality G at rotational speed	G 2.5 at 18,000 rpm
Concentricity	≤ 3 μm
maximum tightening torque $M_{d\max}$	≤ 14 N·m

Accessories

Hexagon screwdriver with T-handle Hexagon 4 mm	627425 4
--	----------