

**3M****Shell-type ear defenders, dependent on noise levels Peltor™ LiteCom™ Plus****Order data**

Order number	097799
GTIN	7318640063310
Item class	04A

**Description****Version:**

High-performance ear defenders dependent on noise levels with integral radio device. Two **level dependent external microphones** transmit environment noise such as voices or warning signals into the shell at a pleasant volume. The incorporated two-way radio technology allows communication with other Peltor™ LiteCom™ shell-type ear defenders and radio devices. The **noise suppressing dynamic voice microphone** permits a simplified communication even in noisy environments. Very high power permits a range is up to three kilometres. The headset works with the registration free PMR 466 standard and therefore has precisely 8 channels in the frequency range from 466 MHz. The three buttons allow **easy operation**, even when wearing gloves. **Voice-activated transmission (VOX)** without pressing any buttons and auto-off function. The external audio input also offers the option of connecting a smartphone. The headset has a **rechargeable 3.7 V lithium ion battery**. SNR = 34 dB (H = 35 dB, M = 32 dB, L = 25 dB).

**Application:**

For communication in noisy, demanding working areas.

**Standard:**

EN 352-4; EN 352-6

**Supplied with:**

With battery, charger, extra hygiene kit and microphone protection.

**Attention:**

German version! Order free UK adapter plug No. 08 1172\_GB

SNR value (noise attenuation): 34 dB(A)

Working time: 20 h

Weight incl. batteries: 464 g

---

## Technical description

Working time	20 h
SNR value (noise attenuation)	34 dB(A)
Weight incl. batteries	464 g
Series	Peltor™ LiteCom