

HOLEX®
Water pump pliers VDE grips, overall length: 250 mm

Order data

Order number	705746 250
GTIN	4045197887887
Item class	72B

Description
Version:

Box joint (= double guides). Designed to prevent fingers being trapped. Induction hardened. Notched serrated jaws, adjustable in stepped holes. Multi-position ratchet adjustment. **Insulated to DIN EN 60900 / VDE 0682-201.**

Pliers chemically blacked, head bright polished, handles insulated with multi-component covering.

Standard:

DIN ISO 8976

Material:

Chrome vanadium steel, drop forged.

electrical insulation: VDE 1000 V

Hexagon across flats: 36 mm

Jaw capacity for pipes: 1.1/2 inch

Technical description

Jaw capacity for pipes	1.1/2 inch
overall length	250 mm
Hexagon across flats	36 mm
Surface	chemically blacked
electrical insulation	VDE 1000 V
Norm	DIN ISO 8976
Norm	DIN EN 60900 / VDE 0682-201

Handle	Multi-component covering
Material	Chrome vanadium steel, drop forged
non-sparking	no
Stepped fine adjustment	no
Self-locking	yes
Protection against trapping fingers	yes