



Wire stripping tool VDE insulated, Overall length: 160 mm



Order data

Order number	728761 160
GTIN	4045197888099
Item class	72B

Description

Version:

Offset jaws with V-shaped cutting edges (up to max. 5 mm external Ø). Laid-in joint with “no-play” action and opening spring. With adjustable screw for cross section adjustment. Handles with multi-component covering, **insulated up to 1000 V to DIN EN 60900 / VDE 0682-201**.

Jaws bright finished.

Material:

Special tool steel, drop-forged and oil-hardened.
electrical insulation: VDE 1000 V

Technical description

overall length	160 mm
electrical insulation	VDE 1000 V
Norm	DIN EN 60900 / VDE 0682-201
Cutter form	Vee cutter
Handle	Multi-component covering
Material	Special tool steel, drop-forged and oil-hardened
Surface	bright finish
with return spring	yes

with adjustable screw for cross section adjustment.

yes