



Straight die grinder Cordless, Manufacturer's designation: M18FDG



Order data

Order number	077280 M18FDG
GTIN	4002395287017
Item class	03L

Description

Version:

Powerful 18 V / 5.0 Ah cordless straight die grinder with brushless POWERSTATE™ motor.

- **REDLINK PLUS™ electronics with digital overload protection for better performance.**
- **REDLITHIUM-ION™ battery with single-cell monitoring.**
- **Universal arbor for all the usual 6 and 8 mm accessories.**
- **Very slim design for increased user comfort.**
- **Exchangeable dust-protection grille protects the motor and prolongs its working life.**
- **Spindle neck with rubber face for extra user comfort.**
- **Restart inhibit.**

Supplied with:

2 × 18 V / 5.0 Ah Red Li-ion batteries, charger, 6 mm collet, 8 mm collet, open ended spanners AF 15 / 17 AF, 2 × dust-protection grilles, HD box.

Note:

For matching spare batteries and accessories see No. 073811ff.

See No. 540200 ff for suitable burrs.

See No. 550600 ff for suitable grinding points.

See No. 551850 ff for suitable polishing points.

Packaging: Modular case (HD=Heavy Duty)

suitable battery - supplier / battery type / voltage: Milwaukee type B 18 V

Manufacturer's designation: M18FDG

Battery voltage: 18 V

Battery capacity: 5 A·h

Speed range: 27 rpm

maximum collet Ø: 6 - 8 mm

Weight: 2.1 kg

Technical description

electronic speed pre-selection	no
Battery capacity	5 A·h
Battery voltage	18 V
maximum vibration to EN	3.4 m/s ²
Manufacturer's designation	M18FDG
maximum collet Ø	6 - 8 mm
Manufacturer ID	HD18SG
Weight	2.1 kg
Speed range	27 rpm
suitable battery - supplier / battery type / voltage	Milwaukee type B 18 V
Packaging	Modular case (HD=Heavy Duty)

Accessories

Battery charger Manufacturer ID M1218C	073840 M1218C
Battery charger Manufacturer ID M1218FC	073840 M1218FC