



Strato precision surface grinding wheel D×W×H (mm), 225×25×51



Order data

Order number	590250
GTIN	9003174414018
Item class	53Y

Description

Version:

High performance surface grinding wheels with high-porosity bonding system for reduced thermal loading and minimal dressing diamond wear.

- **Universally applicable for reciprocating grinding processes, which significantly reduces the frequency of wheel changes in daily operation.**
- **Can be used on all commercially available grinding machines for mould and die making and machine tool building e.g. Jung, ABA, Blohm, Elb, Mägerle, Ziersch&Baltrusch, Geibel&Hotz, Jones&Shipman.**
- **Cooling with emulsion is necessary, ensure good lubrication, especially on long-chipping materials.**

Specially treated Aluminium Oxide for grinding **unalloyed and low alloy unhardened steels.**

Application:

For rough grinding (roughing).

Specification:

F13A46HH11V-Strato steel low alloyed.

Note:

Profile surface grinding wheels available on request.

Grinding process: Surface grinding

Grinding medium code: A

Shape: 1

Shape: 1

Technical description

Grinding process	Surface grinding
Grinding medium code	A
Shape	1
Disc Ø D	225 mm
Disc thickness T	25 mm
Product name attribute	225×25×51
Bore Ø H	51 mm