

HOLEX®
Short drill chuck Form A, SK 40, Clamping range: 2,5-16 mm

Order data

Order number	301565 2,5-16
GTIN	4045197931818
Item class	32K

Description
Version:

For clockwise and anticlockwise rotation.
Burnished. With Balluffchip bore.

Supplied with:

Torx® chuck key with T-handle **for high clamping force.**

Optional extras:

Pull studs (PS) No. 308600 – 308806, PS wrenches No. 308810– 308830.

Arbor standard: DIN 69871

Arbor standard: ISO 7388-1

Shape: A

Balance quality G at rotational speed: G 6.3 at 15,000 rpm

Concentricity: $\leq 50 \mu\text{m}$

maximum tightening torque $M_{d\text{max}}$: $\leq 14 \text{ N}\cdot\text{m}$

Overhang dimension A: 80 mm

External \varnothing D: 50 mm

Spare Torx® screwdriver 625220: TX25

Technical description

Clamping range	2.5 - 16 mm
Overhang dimension A	80 mm
Spare Torx® screwdriver 625220	TX25
External \varnothing D	50 mm

Capacity	SK 40
Arbor standard	DIN 69871
Arbor standard	ISO 7388-1
Shape	A
Balance quality G at rotational speed	G 6.3 at 15,000 rpm
Concentricity	≤ 50 μm
maximum tightening torque $M_{d\max}$	≤ 14 N·m
Balluffchip bore	yes