

HOLEX®**Short drill chuck Form A, HSK-A 100, Clamping range: 2,5-16 mm****Order data**

Order number	307775 2,5-16
GTIN	4045197932013
Item class	32K

Description**Version:**

- **For clockwise and anticlockwise rotation.**
- **With Ballufchip bore.**
- **Slim design.**
- **Specific coolant transfer to tools with IC.**
- **Optimum holding torques at the tool.**

Supplied with:

Clamping wrench with T-handle.

Optional extras:

Socket No. 309890

Coolant feed pipe No. 309880.

Arbor standard: ISO 12164-1

Arbor standard: DIN 69882-7

Arbor standard: DIN 69893-1

Shape: A

Balance quality G at rotational speed: G 6.3 at 15,000 rpm

Concentricity: $\leq 50 \mu\text{m}$

Type: slim

Overhang dimension A: 110 mm

External \varnothing D: 50 mm

Spare Torx® screwdriver 625220: TX25

Technical description

Overhang dimension A	110 mm
Clamping range	2.5 - 16 mm
Spare Torx® screwdriver 625220	TX25
External Ø D	50 mm
Type	slim
Capacity	HSK-A 100
Arbor standard	ISO 12164-1
Arbor standard	DIN 69882-7
Arbor standard	DIN 69893-1
Shape	A
Balance quality G at rotational speed	G 6.3 at 15,000 rpm
Concentricity	≤ 50 µm
maximum tightening torque $M_{d\max}$	≤ 14 N·m