


XOMW060310ZZSR, HB4715, Type: HART

Order data

Order number	212830 HART
GTIN	4045197942579
Item class	21A

Description
Note:

Standard application values for $a_e = 0.5...1 \times D / a_{p\max}$
 recommended cutting depth $a_{p\max}$: 0.5 mm
 maximum cutting depth $a_{p\max}$: 1 mm
 Programming radius at $a_{p\max}$: 2 mm
 Feed f_z per tooth: 0.4 mm

Technical description

Feed f_z per tooth	0.4 mm
maximum cutting depth $a_{p\max}$ when side milling	0.5 mm
Type	HART
Series	High feed rate milling cutter
ISO code indexable insert	XOMW060310ZZSR
Grade	HB4715
Tool material	HM

recommended cutting depth $a_{p\max}$	0.5 mm
maximum cutting depth $a_{p\max}$	1 mm
Programming radius at $a_{p\max}$	2 mm