



Powerful mesh-cutting pincers, black burnished, Overall length: 300 mm



Order data

Order number	706665 300
GTIN	4010995407124
Item class	73D

Description

Version:

Induction hardened cutting edges, approx. 64 HRC. Plastic coated handles.
With special slim head and long handles. High strength precision ground cutting edges.

Application:

Slim and narrow design for twisting difficult-to-access binding wires

Material:

Special tool steel, drop-forged and oil-hardened.
Cutting capability medium hard wire up to \varnothing : 3.8 mm

Technical description

Cutting capability medium hard wire up to \varnothing	3.8 mm
overall length	300 mm
Head	slim
Arm	long
Material	Special tool steel, drop-forged and oil-hardened
Surface	black burnished