



Abrasive flap disc V4 Purple Power, (CER) steel plate, dished for steel and stainless steels, Ø 125 mm, Grit: 36



Order data

Order number	565450 36
GTIN	4027497609314
Item class	53L

Description

Version:

Abrasive flap disc with **high coating density** and sturdy sheet metal pad for high contact pressures. Self-sharpening ceramic grit (CER) on polyester backing for **very high removal rates** and toughness.

Application:

On robot systems or high-power machines (>1700 Watt). For hard and rough grinding work on surfaces and edges.

Grinding medium code: Ceramic

Iron, sulphur and chlorine constituents: < 0.1 %

optimised for material: INOX

optimised for material: Steel

maximum circumferential speed: 80 m/s

Shape description: dished

Bore Ø: 22.23 mm

Technical description

Disc Ø	125 mm
--------	--------

Bore Ø	22.23 mm
Grit	36
Shape description	dished
Grinding media	Ceramic grit (CER)
Grinding medium code	Ceramic
Iron, sulphur and chlorine constituents	< 0.1 %
Product name attribute	Ø 125 mm
optimised for material	INOX
optimised for material	Steel
maximum circumferential speed	80 m/s