


Cordless drill / driver, Manufacturer ID: GSR1821

Order data

Order number	070243 GSR1821
GTIN	3165140920490
Item class	03B

Description
Version:

Bosch cordless drill / driver

- **Compact, powerful cordless drill with forward/reverse operation.**
- **Long service life thanks to brushless EC motor (not 070243).**
- **With Electronic Motor Protection (EMP) and Electronic Cell Protection (ECP).**
- **LED light to illuminate the working area and battery charge display.**
- **Multi-stage torque setting for precise screw driving.**
- **Electronic speed control for precise drilling and screw driving.**
- **Softgrip.**

Outstanding available and comfortable handling due to **compact design**. Motor brake for precise work.

Note:

See No. 073851 ff. and 073866 ff for suitable spare batteries, starter sets and chargers.

Packaging: Modular case (L-Boxx)

suitable battery - supplier / battery type / voltage: Bosch 18 V

Manufacturer's designation: GSR 18V-21

Motor design: 4-pole DC motor

Battery voltage: 18 V

Battery capacity: 2 A·h

maximum torque soft: 21 N·m

maximum torque hard: 55 N·m

Technical description

Speed range 2nd speed	0 - 1800 rpm
maximum twist drill size Ø in wood	35 mm
maximum vibration to EN	<2.5 m/s ²
maximum torque soft	21 N·m
Manufacturer's designation	GSR 18V-21
maximum torque hard	55 N·m
typical application	Medium
Packaging	Modular case (L-Boxx)
Battery capacity	2 A·h
Motor design	4-pole DC motor
maximum twist drill size Ø in steel	13 mm
Quick-clamping chuck range	1.5 - 13 mm
Weight	1.7 kg
suitable battery - supplier / battery type / voltage	Bosch 18 V
Speed range 1st speed	0 - 480 rpm
Battery voltage	18 V

Accessories

Battery charger Manufacturer's designation 1880CV	073866 1880CV
Wireless charging starter set Manufacturer's designation GAL1830W	073862 GAL1830W
Li-ion battery Battery type, battery voltage B18 V	073851 B18