



## Cordless pipe cutter, Manufacturer's designation: C12PC/0



### Order data

Order number	078218 C12PC/0
GTIN	4002395236374
Item class	03L

### Description

#### Version:

**Compact cordless pipe cutter** with stainless cutting head for copper pipe  $\varnothing$  12 – 28 mm.

**Automatic adaptation** to the pipe  $\varnothing$ . **Quick cutting**, e.g. cuts 15 mm  $\varnothing$  copper pipe in less than 3 seconds. Overall width 40 mm, minimum wall clearance 40 mm. Supplied **without batteries and charger**.

#### Attention:

German version. Order free UK adapter plug No. 08 1172\_GB.

#### Note:

Batteries can be found under 073814 ff.

suitable battery - supplier / battery type / voltage: Milwaukee type B 12 V

Battery voltage: 12 V

Speed range: 0 - 500 rpm

maximum pipe  $\varnothing$  copper: 12 - 28 mm

Weight: 1.5 kg

maximum vibration to EN:  $< 2.5 \text{ m/s}^2$

Special features: LED

### Technical description

Battery voltage	12 V
maximum vibration to EN	$< 2.5 \text{ m/s}^2$
Weight	1.5 kg

Manufacturer's designation	C12PC/0
Speed range	0 - 500 rpm
Special features	LED
maximum pipe Ø copper	12 - 28 mm
suitable battery - supplier / battery type / voltage	Milwaukee type B 12 V

---

## Accessories

Li-ion system M4B2/M12B2 Rechargeable battery type, battery voltage MB12 V	073814 MB12
Battery charger Manufacturer ID M1218C	073840 M1218C
Battery charger Manufacturer ID M1218FC	073840 M1218FC