



## Wide drawer with body Drawer usable height 140 mm

Body of sheet metal with a cylinder lock. Drawers of sheet metal with wide aluminium grip handles and labelling strips. Smooth-running drawers, Delrin 100 mm rollers, 28 mm with very good damping characteristics and smooth running, - 90 % extendable.



## Order data

Order number	932601 140
Product name	Wide drawer with body
Type	Drawer usable height 140 mm
GTIN	4045197727930
Pack unit quantity	1

Order number: 932601 140

Material thickness	1 mm
Drawer/pull-out shelf load capacity	100 kg
Drawer runner extension (partial/full extension)	90 %
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Height	180 mm
Width	1200 mm
Depth	630 mm
Drawer usable height	140 mm
Drawer usable width	1090 mm
Drawer usable depth	520 mm
Number of drawers	1
Number of doors	1

Order number: 932601 140

ecl@ss 10.0.1	21-10-04-16	UNSPSC 13.1	24-10-20-06
ecl@ss 9.1	21-10-04-16	UNSPSC 12.0901	24-10-20-06
ecl@ss 9.0	21-10-04-16	UNSPSC 11.2	24-10-20-06
ecl@ss 8.1	21-10-04-16	UNSPSC 9.0501	24-10-20-06
ecl@ss 8.0	21-10-04-16	UNSPSC 8.4	24-10-20-06
ecl@ss 7.1	21-10-04-16	UNSPSC 8.0	24-10-20-06
ecl@ss 7.0	21-10-04-16	UNSPSC 7.5	24-10-20-06
ecl@ss 6.2	21-10-04-16	UNSPSC 7.0901	24-10-20-06
ecl@ss 6.1	21-10-04-16	UNSPSC 7.0401	24-10-20-06
ecl@ss 6.0.1	21-10-04-16	UNSPSC 6.1101	24-10-20-06
ecl@ss 5.1	21-10-04-16	UNSPSC 6.0801	24-10-20-06
ecl@ss 5.0.1	21-10-04-16	UNSPSC 6.0315	24-10-20-06
ecl@ss 4.1	21-10-04-16	UNSPSC 6.0	24-10-20-06
ecl@ss 4.0	21-10-04-16	UNSPSC 5.0301	24-10-20-06
		UNSPSC 5.02	24-10-20-06
		UNSPSC 5.01	24-10-20-06

Order number: 932601 140

---

## **Additional information**

**Colour:** Body light grey RAL 7035, drawer signal blue RAL 5005 **powder-coated.**