




## Set of anti-slip mats 5-piece

Mat with structured surface of PES/glass fibre fabric, coated on both sides with non-slip PVC foam. Very good non-slip and characteristics and tear resistance.



## Order data

Order number	960163
Product name	Set of anti-slip mats 5-piece
Type	
GTIN	2050001854476
Pack unit quantity	1

Order number: 960163

suitable for workstations and storage equipment	Workbench
Thickness	2 – 3 mm
Width	490 mm
Depth	520 mm
Material	PES/glass fibre fabric, coated on both sides with non-slip PVC foam,
Surface	open
Colour	black
Set contents	5

Order number: 960163

ecl@ss 10.0.1	21-10-14-15	UNSPSC 13.1	52-10-15-11
ecl@ss 9.1	21-10-14-01	UNSPSC 12.0901	52-10-15-11
ecl@ss 9.0	21-10-14-01	UNSPSC 11.2	52-10-15-11
ecl@ss 8.1	21-10-14-01	UNSPSC 9.0501	52-10-15-11
ecl@ss 8.0	21-10-14-01	UNSPSC 8.4	52-10-15-11
ecl@ss 7.1	21-10-14-01	UNSPSC 8.0	52-10-15-11
ecl@ss 7.0	21-10-14-01	UNSPSC 7.5	52-10-15-11
ecl@ss 6.2	21-10-14-01	UNSPSC 7.0901	52-10-15-11
ecl@ss 6.1	21-10-14-01	UNSPSC 7.0401	52-10-15-11
ecl@ss 6.0.1	21-10-14-01	UNSPSC 6.1101	52-10-15-11
ecl@ss 5.1	21-10-91-05	UNSPSC 6.0801	52-10-15-11
ecl@ss 5.0.1	21-10-91-05	UNSPSC 6.0315	52-10-15-11
ecl@ss 4.1	21-10-09-05	UNSPSC 6.0	52-10-15-11
ecl@ss 4.0	21-10-09-05	UNSPSC 5.0301	52-10-15-11
		UNSPSC 5.02	52-10-15-11
		UNSPSC 5.01	52-10-15-11

Order number: 960163

---

## Additional information

**Suitable for:** Drawers No. 920140, No. 933730, No. 933760, No. 934194 and drawers for workbenches No. 920000, No. 920010, No. 930950 – 933427, No. 933500 – 933900, No. 934400 – 934650 and No. 934100 – 934170.

**Suitable for:** For housing width **600 mm**. For internal drawer dimensions 490×520 mm.

---

## Note

No adhesive/non-slip effect when wet.

---

## Approvals

DIN EN 597-1 / 6.4 (flame resistance test); VDI 2700:2009 / sheet 15 / point 11.3 (deformation and impression behaviour).