

HOLEX®
Flap wheel roller M14 Fleece/fabric, Ø 100 × 50 mm, Grit equivalent: 80CRS

Order data

Order number	566372 80CRS
GTIN	4045197924605
Item class	52M

Description
Version:

Strips arranged in a fan form around the axis of the tool. **M14 direct mounting.**

Combination of **abrasive cloth and fleece.**

Application:

Removes scratches, gives a brushed matt effect.

Grinding medium code: A

Iron, sulphur and chlorine constituents: < 0.1 %

Thread: M14

optimised for material: Steel

optimised for material: INOX

maximum circumferential speed: 30 m/s

recommended speed: 2800 rpm

maximum speed: 6000 rpm

Technical description

recommended speed	2800 rpm
Grit equivalent	80

maximum speed	6000 rpm
Grinding medium code	A
Iron, sulphur and chlorine constituents	< 0.1 %
Thread	M14
Roller Ø	100 mm
Roller width	50 mm
Product name attribute	Ø 100 × 50 mm
optimised for material	Steel
optimised for material	INOX
maximum circumferential speed	30 m/s