



XDMW120516ZDSR, HB4715, Type: HART

Order data

Order number	212891 HART
GTIN	4045197943194
Item class	21A

Description
Note:

Standard application values for $a_e = 0.5...1 \times D / a_{p,max}$
 recommended cutting depth $a_{p,max}$: 0.8 mm
 maximum cutting depth $a_{p,max}$: 2 mm
 Programming radius at $a_{p,max}$: 3 mm
 Feed f_z per tooth: 0.9 mm

Technical description

Feed f_z per tooth	0.9 mm
Type	HART
maximum cutting depth $a_{p,max}$ when side milling	0.8 mm
Series	High feed rate milling cutter
ISO code indexable insert	XDMW120516ZDSR
Grade	HB4715
Tool material	HM

recommended cutting depth $a_{p\max}$	0.8 mm
maximum cutting depth $a_{p\max}$	2 mm
Programming radius at $a_{p\max}$	3 mm