




Precision surface grinding wheel D×W×H (mm), 225×25×51, Type: A60



Order data

Order number	591710 A60
GTIN	9003176643836
Item class	53Y

Description

Version:

High performance surface grinding wheels with high-porosity bonding system for reduced thermal loading and minimal dressing diamond wear.

- **Universally applicable for reciprocating grinding processes, which significantly reduces the frequency of wheel changes in daily operation.**
- **Can be used on all commercially available grinding machines for mould and die making and machine tool building e.g. Jung, ABA, Blohm, Elb, Mägerle, Ziersch&Baltrusch, Geibel&Hotz, Jones&Shipman.**
- **Cooling with emulsion is necessary, ensure good lubrication, especially on long-chipping materials.**

High-performance line with sintered carborundum for **longer working life, freer cutting** and cooler grinding. Particularly suitable for high-alloy hardened steels, stainless steel and high-speed steels with a hardness of 60 HRC. The next higher quality step is offered by the VIB-STAR CBN super-abrasive CBN grinding wheels.

Application:

- **Universally applicable for reciprocating grinding processes, which significantly reduces the frequency of wheel changes in daily operation.**
- **Can be used on all commercially available grinding machines for tool and die making and machine tool building e.g. Jung, ABA, Blohm, Elb, Mägerle, Ziersch&Baltrusch, Geibel&Hotz, Jones&Shipman.**

- **Cooling with emulsion is necessary, ensure good lubrication, especially on long-chipping materials.**

Specification:
454A60J10V3.

Note:

Profile surface grinding wheels available on request.

Grinding process: Surface grinding

Grinding medium code: Ceramic

Shape: 1

Shape: 1

Technical description

Grinding process	Surface grinding
Grinding media	Ceramic grit (CER)
Grinding medium code	Ceramic
Specification	454A60J10V3
Shape	1
Disc Ø D	225 mm
Disc thickness T	25 mm
Product name attribute	225×25×51
Bore Ø H	51 mm